

Family

Haddoc

Design – Johan Lindstén



JOHANSON



Introduction

The idea behind Haddoc was to create a series of seating furniture that is so inviting and comfortable that it promotes relaxing breaks in an ergonomic sitting position. Comfort was key to the design process where an air of lightness and strong character form the basis of Haddoc.



Designer

Johan Lindstén's products are characterised by well-thought out design and unexpected details in a creative process that optimises function. Johan wants his designs to interact with their surroundings in a way that influences the mood of the user. He draws his inspiration from the most unlikely of sources, such as the lilac bush outside his home or the Ocean of Storms on the moon.



Models



Haddoc Oyster 05-46*



Haddoc Oyster WA 05-46*



Haddoc Oyster WA 05-46
Wheels, tilt mechanism height adj



Haddoc Oyster 08-46



Haddoc Oyster WA 08-46



Haddoc Oyster 10-46



Haddoc Oyster WA 10-46



Haddoc Shell 09-46



Haddoc Shell WA 09-46



Haddoc EC

* Available with tilt mechanism and height adjustment

Material

Seat - Upholstery materials

Johanson offers a very generous range of fabrics, leather and artificial leather from the most reputable suppliers in the world. Should any other material be desired despite the wide selection, it is also possible to suggest other materials. Johanson does not charge start-up costs for handling non-standard materials

Multicolour - Finish RAL

Take part in Johanson's color range, 400 variants of different finishes are offered as standard on steel frames and metal details. Choose from all 192 RAL colors, alternatives are available both as solid finish (gloss 72) or Structure finish which has a matte, slightly textured elegant surface. In addition, 15 RAL colors with pearl finish and chrome are offered.

For all colours see www.johansondesign.com

192 Solid collection (gloss 72)

192 Structure collection (matte, textured surface)

15 Pearl finish collection and chrome.



Accessories




Connector

08-base



Connector

09-base



Extra

Wheels, tilt mechanism and height adjustment for 05-base.
Felt gliders



Stacking trolley

Stackability for each chair can be found under facts.



Wheels

Wheels for 05-base in black, white and chrome.

Facts

Material

The seat is made in moulded CMHR foam (density 65kg) that meets the highest requirements for flammability (CMHR quality). The base is made of finished/lacquered metal.

Certificate

- Fire certificate (Danak)



BIM - objects can be downloaded
at johansondesign.com



3D Max



Autocad 2D



Archicad



Autocad 3D



Revit



Sketchup

 pCon

Recycling

All steel parts are recyclable.

Before we finish the chrome/lacquer all grease/oil is removed by alkaline wash and then sent for destruction. The lacquering is produced by electrostatic epoxy powder coating that gives a minimum of waste. The electrostatic chrome (chrome 3) is recyclable. The plastic parts that are used are recyclable by grinding. All upholstery and frames of synthetic material are totally without C.F.C. emissions. All glue is water based.


Material declaration

For more information about the product please download material declaration on our website, under Downloads à Product Information at www.johansondesign.com



Facts

Measurements cm




Haddoc Oyster 05-46

Weight (kg)	12,0
Volym (m ³)	0,32
Height with height adjustment	80-88
Seat height with height adjustment	43-51

The facts also apply to model with tilt and height adjustment.

Measurements cm




Haddoc Oyster WA 05-46

Weight (kg)	12,0
Volym (m ³)	0,32
Height with height adjustment	80-88
Seat height with height adjustment	43-51

The facts also apply to model with tilt and height adjustment.


Measurements cm



Haddoc Oyster 08-46

Weight (kg)	12
Volym (m ³)	0,266


Measurements cm



Haddoc Oyster WA 08-46

Weight (kg)	12
Volym (m ³)	0,266

Measurements cm




Haddoc Oyster 10-46

Weight (kg)	14
Volym (m ³)	0,266

Facts


Measurements cm



Haddoc Oyster WA 10-46

Weight (kg) 14
Volym (m³) 0,266

Measurements cm




Haddoc Shell 09-46

Weight (kg) 9,0
Volym (m³) 0,24



Measurements cm




Haddoc Shell WA 09-46

Weight (kg) 9,0
Volym (m³) 0,24



Measurements cm



Haddoc EC

Weight (kg) 12
Volym (m³) 0,51









JOHANSON

Johanson Design AB | Anders Anderssons Väg 7 | 285 35 Markaryd | Sweden
Tel +46-433 725 00 | www.johansondesign.com