

Family

# Haddoc

Design – Johan Lindstén



**JOHANSON**



## Introduction

The idea behind Haddoc was to create a series of seating furniture that is so inviting and comfortable that it promotes relaxing breaks in an ergonomic sitting position. Comfort was key to the design process where an air of lightness and strong character form the basis of Haddoc.



## Designer

Johan Lindstén's products are characterised by well-thought out design and unexpected details in a creative process that optimises function. Johan wants his designs to interact with their surroundings in a way that influences the mood of the user. He draws his inspiration from the most unlikely of sources, such as the lilac bush outside his home or the Ocean of Storms on the moon.



# Models

---



Haddoc Oyster 05-46\*



Haddoc Oyster WA 05-46\*



Haddoc Oyster WA 05-46  
Wheels, tilt mechanism height adj



Haddoc Oyster 08-46



Haddoc Oyster WA 08-46



Haddoc Oyster 10-46



Haddoc Oyster WA 10-46



Haddoc Shell 09-46



Haddoc Shell WA 09-46



Haddoc EC  
Woven back is available in  
black and beige.

\* Available with tilt mechanism and height adjustment

# Material

---

## Seat - Upholstery materials

Johanson offers a very generous range of fabrics, leather and artificial leather from the most reputable suppliers in the world. Should any other material be desired despite the wide selection, it is also possible to suggest other materials. Johanson does not charge start-up costs for handling non-standard materials.

Haddoc EC - Woven back is available in black and beige.

## Multicolour - Finish RAL

Take part in Johanson's color range, 405 variants of different finishes are offered as standard on steel frames and metal details. Choose from all 195 RAL colors, alternatives are available both as solid finish (gloss 72) or Structure finish which has a matte, slightly textured elegant surface. In addition, 15 RAL colors with pearl finish and chrome are offered.

For all colours see [www.johansondesign.com](http://www.johansondesign.com)

**195 Solid collection** (gloss 72)

**195 Structure collection** (matte, textured surface)

**15 Pearl finish collection** and chrome.



# Accessories

---




## Connector

08-base



## Connector

09-base



## Extra

Wheels, tilt mechanism and height adjustment for 05-base.  
Felt gliders



## Stacking trolley

Stackability for each chair can be found under facts.



## Wheels

Wheels for 05-base in black, white and chrome.

# Facts

---

## Material

The seat is made of FSC certified wood and padding is made of polyether/foam. Finished/lacquered metal.

## Fire classification

All products meet Möbelfakta's fire requirements. All polyether/foam are tested to Cal TB 117. All standard fabrics meet EN 1021:1 & 2. Other classification, for example BS 5856 (Crib 5) on request, please contact customer support.

## Certificate




## Recycling

All steel parts are recyclable. Before we finish the chrome/lacquer all grease/oil is removed by alkaline wash and then sent for destruction. The lacquering is produced by electrostatic epoxy powder coating that gives a minimum of waste. The electrostatic chrome (chrome 3) is recyclable. The plastic parts that are used are recyclable by grinding. All upholstery and frames of synthetic material are totally without C.F.C. emissions. All glue is water based.


## BIM - objects can be downloaded

at [johansondesign.com](http://johansondesign.com)



# Facts

Measurements cm




## Haddoc Oyster 05-46

|                                    |       |
|------------------------------------|-------|
| Weight (kg)                        | 12,0  |
| Volym (m <sup>3</sup> )            | 0,32  |
| Height with height adjustment      | 80-88 |
| Seat height with height adjustment | 43-51 |

The facts also apply to model with tilt and height adjustment.

Measurements cm




## Haddoc Oyster WA 05-46

|                                    |       |
|------------------------------------|-------|
| Weight (kg)                        | 12,0  |
| Volym (m <sup>3</sup> )            | 0,32  |
| Height with height adjustment      | 80-88 |
| Seat height with height adjustment | 43-51 |

The facts also apply to model with tilt and height adjustment.


Measurements cm



## Haddoc Oyster 08-46

|                         |       |
|-------------------------|-------|
| Weight (kg)             | 12    |
| Volym (m <sup>3</sup> ) | 0,266 |


Measurements cm



## Haddoc Oyster WA 08-46

|                         |       |
|-------------------------|-------|
| Weight (kg)             | 12    |
| Volym (m <sup>3</sup> ) | 0,266 |

Measurements cm




## Haddoc Oyster 10-46

|                         |       |
|-------------------------|-------|
| Weight (kg)             | 14    |
| Volym (m <sup>3</sup> ) | 0,266 |

# Facts


Measurements cm



**Haddoc Oyster WA 10-46**

Weight (kg) 14  
Volym (m<sup>3</sup>) 0,266

Measurements cm




**Haddoc Shell 09-46**

Weight (kg) 9,0  
Volym (m<sup>3</sup>) 0,24



Measurements cm




**Haddoc Shell WA 09-46**

Weight (kg) 9,0  
Volym (m<sup>3</sup>) 0,24



Measurements cm



**Haddoc EC**

Weight (kg) 12  
Volym (m<sup>3</sup>) 0,51









# JOHANSON

---

Johanson Design AB | Anders Anderssons Väg 7 | 285 35 Markaryd | Sweden  
Tel +46-433 725 00 | [www.johansondesign.com](http://www.johansondesign.com)